


**DIN 934** similar to ISO 4032

## Hexagon nuts

External hex

Steel 8 | nickel plated | Cr(VI)-free | Metric thread

Further information: DIN-standard has been withdrawn | changed spanner widths for M10, M12, M14 and M22 | the fine thread has been transferred to ISO 8673



Diameter (d)	d <sub>a</sub>		d <sub>w</sub> min.	e min.	m		s		Pitch (P)
	min.	max.			min.	max.	min.	max.	
M 2	2.0	2.30	3.2	4.32	1.35	1.6	3.82	4.0	0.40
M 2.5	2.5	2.50	4.1	5.45	1.75	2.0	4.82	5.0	0.45
M 3	3.0	3.45	4.5	6.01	2.15	2.4	5.32	5.5	0.50
M 4	4.0	4.60	5.8	7.66	2.90	3.2	6.78	7.0	0.70
M 5	5.0	5.75	6.8	8.79	3.70	4.0	7.78	8.0	0.80
M 6	6.0	6.75	8.8	11.05	4.70	5.0	9.78	10.0	1.00
M 10	10.0	10.80	15.3	18.90	7.64	8.0	16.73	17.0	1.50
M 12	12.0	13.00	17.2	21.10	9.64	10.0	18.67	19.0	1.75
M 16	16.0	17.30	22.2	26.75	12.30	13.0	23.67	24.0	2.00

All technical data refer to the measure mm

