

# ECONOMY URETHANES

**RoHS** AE (Standard type)

D	D <sub>T</sub>	d <sub>T</sub>	L <sub>T</sub>
15			
20			
25	±0.2		±0.3
30		±0.2	
40			
50	±0.3		±0.5
60			

Product guide P.1501 Products data P.1517 Shore A90


F=L×15%		F=L×20%		F=L×25%		d	Catalog No.	Base unit price 1 ~ 19 pieces
F mm	Load N (kgf)	F mm	Load N (kgf)	F mm	Load N (kgf)			
3.8		5		6.3		7	AE 15 - 25	Quotation
4.5	539 { 55}	6	735 { 75}	7.5	932 { 95}	7	30	
5.3		7		8.8		7	35	
6		8		10		7	40	
3.8		5		6.3		8.5	AE 20 - 25	
4.5	1079 { 110}	6	1373 { 140}	7.5	1667 { 170}	8.5	30	
5.3		7		8.8		8.5	35	
6		8		10		8.5	40	
3.8		5		6.3		11	AE 25 - 25	
4.5		6		7.5		11	30	
5.3	1569 { 160}	7	2059 { 210}	8.8	2550 { 260}	11	35	
6		8		10		11	40	
6.8		9		11.3		11	45	
7.5		10		12.5		11	50	
4.5		6		7.5		14	AE 30 - 30	
5.3		7		8.8		14	35	
6		8		10		14	40	
6.8	2452 { 250}	9	2844 { 290}	11.3	3334 { 340}	14	45	
7.5		10		12.5		14	50	
8.3		11		13.8		14	55	
9		12		15		14	60	
6		8		10		14	AE 40 - 40	
7.5	4315 { 440}	10	5099 { 520}	12.5	5982 { 610}	14	50	
9		12		15		14	60	
7.5		10		12.5		14	AE 50 - 50	
9	7355 { 750}	12	8728 { 890}	15	10297 { 1050}	14	60	
12		16		20		14	80	
7.5		10		12.5		14	AE 60 - 50	
9	12356 { 1260}	12	14318 { 1460}	15	16769 { 1710}	14	60	
12		16		20		14	80	

●Load (kgf) = Load (N)×0.101972

**Order** Catalog No. AE 15-25

**Days to Ship** Quotation

**Price** Quotation



**RoHS** LAE

D	D <sub>T</sub>	d <sub>T</sub>	L <sub>T</sub>
8			
10			
15			
20	±0.2		±0.2
25			
30		±0.2	
40			
50	±0.3		±0.5
60			

Product guide P.1501 Shore A90

d	Catalog No. Type D-L	Catalog No. Type D-L	Base unit price 1 ~ 19 pieces
—	—	CE 8-200	Quotation
—	—	CE 10-200	
7	LAE 15-200	CE 15-200	
8.5	LAE 20-200	CE 20-200	
11	LAE 25-200	CE 25-200	
14	LAE 30-500	CE 30-500	
	LAE 40-500	CE 40-500	
	LAE 50-500	CE 50-500	
	LAE 60-500	CE 60-500	

**Order** Catalog No. LAE 30-500

**Days to Ship** Quotation

**Price** Quotation

**RoHS** Configurable full length type AEX

D	D <sub>T</sub>	d <sub>T</sub>	L <sub>T</sub>
8			
10			
15			
20	±0.2		±0.3
25			
30		±0.2	
40			
50	±0.3		±0.5
60			

Product guide P.1501 Shore A90

d	Catalog No.	D	L 1mm increments	Base unit price 1 ~ 19 pieces							
				L10 ~ 20	L21 ~ 40	L41 ~ 60	L61 ~ 80	L81 ~ 100	L101 ~ 150	L151 ~ 200	
—	CEX	8	10 ~ 200								
—		10									
7		15									
8.5	AEX	20									
11		25									
14		30									
	40										
	50										
	60										

**Order** Catalog No. AEX 20 - 52

**Days to Ship** Quotation

**Price** Quotation