



DIN 1530
1.2344 équivalent
Trempe

TIGES DE CŒUR DROIT

— TYPE D'OUTIL STANDARD —



N° de Pièce	M Matériau	H Dureté	T D Tolérance
D-CPD	1.2344 équivalent	48~52HRC	g6



$R \leq 0.5(D \leq 2 \dots R \leq 0.3)$

$H -0.3$

$T -0.02$

$L +2 / +0$

D_{g6}

H	T	N° de Pièce		L
		Type d'outil	D	
2.5	1.2	D-CPD	1	125
3	1.5		1.5	
4	2		2	
5			2.5	
6	3		3	
7			3.5	
8			4	
10	5		4.5	
12			5	
14			6	
			8	


 Commande **N° de Pièce** — **L**
D-CPD2.5 — **125**